



STARLINE® SSP#Q System power inserter to add 60 Vac to 90 Vac to the cable system

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Supports DOCSIS® 3.1 expanded bandwidth up to 1218 MHz
- Supports existing install base with backward compatible faceplates
- Superior flexibility in installation with rotatable faceplate and swivel center seizure mechanism
- Easily configured to enable or block AC power as needed in the network
- Protect valuable network equipment investment with optional heavy surge suppression in Power Inserter

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Power inserter
Product Series	SSP-Q
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Location of Manufacturing	Waived per BABA waiver for BEAD Program
----------------------------------	---

Dimensions

Height	140.462 mm 5.53 in
Depth	63.5 mm 2.5 in
Length	140.462 mm 5.53 in

Electrical Specifications

Current Handling, ac ports	20 A
Current Handling, RF ports	15 A
Operating Frequency Band	5 – 1218 MHz
Surge Protection	No

Environmental Specifications

Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

Packaging and Weights

Weight 0.757 kg | 1.67 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

