

# F112HMS2

---



FlexTwist® Flexible Twist for WR112, 7.05–10.0 GHz, with interface types PDR84 and UBR84, 600 mm

## Product Classification

<b>Product Type</b>	Rectangular waveguide, flexible twist
<b>Product Brand</b>	FlexTwist®

## General Specifications

<b>Component</b>	Flexible Twist
<b>Interface</b>	PDR84
<b>Interface 2</b>	UBR84

## Dimensions

<b>Length</b>	600 mm   23.622 in
<b>Waveguide Size</b>	WR112   WG15   R84

## Electrical Specifications

<b>Attenuation</b>	0.4 dB/m   0.122 dB/ft
<b>Average Power</b>	1260 W
<b>Operating Frequency Band</b>	7.05 – 10.0 GHz
<b>Peak Power</b>	315 kW
<b>VSWR</b>	1.1

## Mechanical Specifications

<b>Minimum Bend Radius, Multiple Bends (E Plane)</b>	76 mm   2.992 in
<b>Minimum Bend Radius, Multiple Bends (H Plane)</b>	152 mm   5.984 in
<b>Maximum Twist</b>	264 °/m   80.467 °/ft
<b>Pressurization, maximum</b>	0.241 N/mm <sup>2</sup>   35 psi

## Regulatory Compliance/Certifications

# F112HMS2

---

**Agency**

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

**Classification**

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

