884015814/10 | CS34R GRY C6 4/23 U/UTP CPK 1KFT

CS34R ETL Verified Category 6 U/UTP Cable, non-plenum, gray jacket, 4 pair count, 1000 ft (305 m) length, CommPak

Product Classification

Regional Availability	Asia | Australia/New Zealand | EMEA | Latin America
Portfolio	NETCONNECT®
Product Type	Twisted pair cable

General Specifications

Product Number	CS34R
ANSI/TIA Category	6
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Gray
Note	All electrical transmission tests include swept frequency measurements
Pairs, quantity	4
Separator Type	Tape separator
Transmission Standards	ANSI/TIA-568-C.2 | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class E

Dimensions

Cable Length	1000 ft | 304.8 m
Diameter Over Jacket, nominal	0.22 in | 5.588 mm
Jacket Thickness	0.02 in | 0.508 mm
Conductor Gauge, singles	23 AWG

Cross Section Drawing

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 25, 2020

884015814/10 | CS34R GRY C6 4/23 U/UTP CPK 1KFT



Electrical Specifications

Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	8 ohms/100 m | 2.438 ohms/100 ft
Delay Skew, maximum	30 ns
Dielectric Strength, minimum	1500 Vac | 2500 Vdc
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	250 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 25, 2020

	CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Enterprise Copper Cable Performance

Frequency (MHz)	IL, typical	NEXT, typical	ACR, typical	PSNEXT, typical	PSACR, typical	ACRF, typical	PSACRF, typical	RL, typical
1.0	1.8	89.3	87.6	87	85.3	84.3	82.4	34
4.0	3.5	80	76.5	77.7	74.1	72.6	70.8	33.9
8.0	5	75.5	70.5	73.2	68.2	66.8	64.9	35.5
10.0	5.6	73.9	68.3	71.5	65.9	64.9	63	36.5
16.0	7.2	70.6	63.4	68.3	61.1	60.8	58.9	37.6
20.0	8.1	69.2	61.2	66.9	58.8	58.9	56.9	38.2
25.0	9	67.6	58.6	65.3	56.2	57	55	38.2
31.25	10.1	66.3	56.1	63.9	53.8	55	53	38.3
62.5	14.5	61.4	46.9	59	44.5	48.9	46.9	34.7
100.0	18.6	58.1	39.5	55.7	37.1	44.7	42.8	31.6
155.0	23.5	55.7	32.2	53	29.5	41	39	29.6
200.0	26.9	52.6	25.7	50.4	23.4	38.6	36.7	29.3
250.0	30.3	50.8	20.5	48.6	18.3	36.5	34.7	28.8
300.0	33.5	49	15.6	46.8	13.4	34.5	32.6	28.9
350.0	36.4	47.6	11.2	45.4	9	33	31	29
400.0	39	46.3	7.3	44.1	5.1	31.3	29.3	30.3
500.0	44.3	43.2	-1.1	41.2	-3.1	27.3	25.5	31
550.0	44.6	43.1	-0.5	41.2	-2.5	27.4	25.5	31
650.0	51.3	40.2	-11.1	38.4	-12.9	22.3	20.4	25

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC
Separator Material	Polyolefin

Mechanical Specifications

Pulling Tension, maximum	25 lb | 11.34 kg

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 25, 2020

884015814/10 | CS34R GRY C6 4/23 U/UTP CPK 1KFT

Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Non-plenum
Flame Test Method	CMR | NEC Article 800 | UL 1666 | UL 444

Packaging and Weights

Cable weight	23.58 lb/kft | 3.26 kg/km
Packaging Type	CommPak® box

Regulatory Compliance/Certifications

Agency	**Classification**
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 25, 2020