## 193746-000 | FIST-GPST-12-AAA-2



FIST GPST Fiber Patch Tray, 12 ports, SC/UPC, singlemode, 19 in, gray, left /right patch cord routing

### Product Classification

Regional Availability	EMEA
Product Type	Fiber patch tray
Product Brand	FIST®
Product Series	FIST-GPST

## General Specifications

Patching
Gray
SC/UPC
Front, left side   Front, right side
12
0
12

## Dimensions

Height	18 mm   0.709 in
Width	355 mm   13.976 in
Depth	190 mm   7.48 in

### **Optical Specifications**

Fiber Mode

Singlemode

## Environmental Specifications

#### **Operating Temperature**

-5 °C to +45 °C (+23 °F to +113 °F)

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023



# 193746-000 | FIST-GPST-12-AAA-2

#### Storage Temperature

-30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** 

Up to 93%, non-condensing

## Packaging and Weights

Packaging quantity

## 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

