404950-000 | FIST-GPST-12-EAN-2



FIST GPST Fiber Patch/Splice Tray, 12/24 ports, no adapters, SMOUV splice chip, 19 in, gray, left patch cord routing

Product Classification

Regional Availability EMEA

Product Type Fiber patch/splice tray

Product Brand FIST®

Product Series FIST-GPST

General Specifications

Functionality Patching | Splicing

Color Gray

Interface, front Unloaded

Patch Cord Entry Location Front, left side

Splicing Type Heat shrink, single fiber fusion

Total Ports, quantity 12

Dimensions

 Height
 18 mm | 0.709 in

 Width
 355 mm | 13.976 in

 Depth
 190 mm | 7.48 in

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -5 °C to +45 °C (+23 °F to +113 °F) Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Page 1 of 2

404950-000 | FIST-GPST-12-EAN-2

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

