CC4198-000 | FIST-GPST-12-AAE1-2



FIST GPST Fiber Patch Tray, 12 ports, LSH/UPC, singlemode, 19 in, gray, left/right patch cord routing

Product Classification

Regional Availability	EMEA
Product Type	Fiber patch tray
Product Brand	FIST®
Product Series	FIST-GPST

General Specifications

Patching
Gray
LSH/UPC
Front, left side Front, right side
12
0
12

Dimensions

Height	18 mm 0.709 in
Width	355 mm 13.976 in
Depth	190 mm 7.48 in

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Operating Temperature

-5 °C to +45 °C (+23 °F to +113 °F)

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023



CC4198-000 | FIST-GPST-12-AAE1-2

Storage Temperature

-30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity

Up to 93%, non-condensing

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

