### EH6496-000 | TENIO-B6-S12-4-N



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 4 pre-installed 12-splice trays

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

#### **Product Classification**

Regional Availability EMEA

Product Type Single-ended, rectangular fiber closure

Product Brand TENIO™
Product Series TENIO

General Specifications

Cable Entry Drop Port StyleGel blockCable Entry Main Port StyleGel block

**Cable Ports Quantity, total** 6 multi-out ports (30 cables)

Cable Sealing TypeCompressed gel

Closure Sealing Type Side latch

Closure Style Single-ended

Color Black
Mounting Wall

Network Area Type Distribution | Drop

Splice Tray Included, quantity 4

**Splice Tray Type Included** 12-way, heat shrink

Splices per Tray, quantity 12
Splicing Capacity, Single Fusion, maximum 144

**Splicing Type, Supported** Single fusion

**Dimensions** 

 Height
 230 mm | 9.055 in

 Width
 134 mm | 5.276 in

Page 1 of 3




## EH6496-000 | TENIO-B6-S12-4-N

**Length** 389 mm | 15.315 in

Main Cable Diameter, maximum 16 mm | 0.63 in

#### Ordering Tree



#### Material Specifications

Material Type Impact-resistant polymer

### **Environmental Specifications**

Environmental Space Below ground | Buried

**Qualification Standards** IEC 61300, 2 m waterhead

Packaging and Weights

Packaging quantity 1

Packaging TypeBox| CartonWeight, net1 kg | 2.205 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



# EH6496-000 | TENIO-B6-S12-4-N





Page 3 of 3

