


FPX-24MPRSOZ



FPX Fiber Optic MPO Module, Singlemode OS2, 24 fiber LC/APC adapter, right, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a “grow as you go” approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	FPX

General Specifications

Functionality	Breakout
Application	For use with FPX panels
Adapter Color	Green
Adapters, quantity, front	12
Adapters, quantity, rear	2
Body Style	Duplex Right orientation
Color, front	Putty white
Color, housing	Putty white
Color, rear	Putty white
Interface, front	LC/APC
Interface, rear	MPO
Interface Feature, rear	APC
Polarity	Pairs, straight
Total Ports, quantity, front	24


Dimensions

Height	33.02 mm 1.3 in
---------------	-------------------

FPX-24MPRSOZ

Width	176.53 mm 6.95 in
Depth	127 mm 5 in

Ordering Tree



¹ SC only
² LC only

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

FPX-24MPRSOZ

ROHS	Compliant/Exempted
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant/Exempted

