

NGF-MPMROT408



Next Generation Frame (NGF) Fiber Termination Block, 96 SC/UPC, multimode, right oriented, putty white, MPO at rear end

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch block
Product Series	NGF

General Specifications

Functionality	Patching
Application	Used in NGF-style frames only
Body Style	Right orientation
Color	Putty white
Color, front	Putty white
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	MPO
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	96

Dimensions

Height	239.268 mm 9.42 in
Width	153.416 mm 6.04 in
Depth	434.34 mm 17.1 in

Material Specifications

NGF-MPMROT408

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

