PH3830-000 | FIST-GPST-12-FAN-N



FIST GPST Fiber Termination/Splice Tray, 12/24 ports, no adapters, ANT splice chip, 19 in, gray, left patch cord routing

Product Classification

Regional Availability EMEA

Product Type Fiber patch/splice tray

Product Brand FIST®

Product Series FIST-GPST

General Specifications

Functionality Patching | Splicing

Color Gray

Interface, front Unloaded

Patch Cord Entry Location Front, left side

Splicing Type ANT, single fiber fusion

Total Ports, quantity 12

Dimensions

 Height
 18 mm | 0.709 in

 Width
 355 mm | 13.976 in

 Depth
 190 mm | 7.48 in

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-5 \degree \text{C to } +45 \degree \text{C (} +23 \degree \text{F to } +113 \degree \text{F)}$ Storage Temperature $-30 \degree \text{C to } +60 \degree \text{C (} -22 \degree \text{F to } +140 \degree \text{F)}$

Page 1 of 2



PH3830-000 | FIST-GPST-12-FAN-N

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Packaging quantity

