## RDT-SJ12J00D5002A



RapidFiber® FDT Distribution Terminal, SC/APC, 12-fiber, MPO at far end, 500 ft

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution terminal

Product Brand RapidFiber®

Product Series FDT

### General Specifications

**Functionality** Patching

Adapters, quantity 12

Cable Color Ivory

**Cable Type** Pigtails - Stranded

**Color** Putty white

Interface SC/APC

**Interface, stub** MP0

**Mounting** Wall

Port, quantity 12

### Dimensions

 Height
 152.4 mm | 6 in

 Width
 228.6 mm | 9 in

 Depth
 101.6 mm | 4 in

 Cable Length
 152.4 m | 500 ft

 Outer Cable Diameter
 3 mm | 0.118 in

Material Specifications



# RDT-SJ12J00D5002A

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

**Environmental Specifications** 

Environmental Space Indoor

**Qualification Standards** NEMA, Type 12

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

