# RDT-SM12N00D0309A



RapidFiber® Mini-RDT Distribution Terminal, 12-fiber, SC/UPC, Indoor /outdoor cable, 100 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

### Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Brand	RapidFiber®
Product Series	Mini-RDT

## General Specifications

Adapters, quantity	12
Cable Entry Location	Bottom left   Bottom right
Cable Type	Indoor/outdoor - Stranded
Color	Gray
Interface	SC/UPC
Interface, stub	MPO
Mounting	Wall
Port, quantity	12

### Dimensions

Height	200 mm   7.874 in
Width	140 mm   5.512 in
Depth	60 mm   2.362 in
Cable Length	30.48 m   100 ft
Outer Cable Diameter	4 mm   0.157 in


### Dimension Drawing

Page 1 of 3


©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



## RDT-SM12N00D0309A



## Ordering Tree



Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

152 meters (500') 168 meters (550') 183 meters (600') 198 meters (650')



## RDT-SM12N00D0309A

### Material Specifications

Material Type

Plastic

#### **Optical Specifications**

Fiber Mode

Singlemode

### **Environmental Specifications**

Environmental Space Indoor

### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

