



LSA-PLUS® Series 2 Disconnection Module, 10-pair, PROFIL mounting

- Based on genuine LSA-PLUS® connection technology for use in all xDSL and ADSL2+ circuits
- Offer disconnection points for opening the line, testing in both directions or insertion of graded protection elements
- Robust long-term environmental stability allows both indoor and outdoor installation
- Compatible with accessories such as overvoltage protection magazines, labels, test and - connection cords

Product Classification

Regional Availability	EMEA
Product Type	Disconnection module
Product Brand	LSA-PLUS®
Product Series	LSA-PLUS Series 2

General Specifications

Color	Beige
Mounting	PROFIL rods
Pairs, quantity	10
Termination Punchdowns, minimum	200 times
Termination Tool	LSA-PLUS Punchdown tool
Termination Type	IDC

Dimensions

Width	124 mm 4.882 in
Compatible Conductor Gauge, solid	26–20 AWG
Compatible Conductor Gauge, stranded	26–22 AWG

Electrical Specifications

Contact Resistance, maximum	1 mOhm
Current Rating, maximum	2 A
Dielectric Strength	3 kV
Insulation Resistance, minimum	50 GOhm

Material Specifications

60891121-02 | 60891121-02

Contact Base Material	Brass
Contact Plating Material	Silver
Material Type	Polybutylene terephthalate (PBT)

Mechanical Specifications

Plug Insertion Life, minimum	250 times
-------------------------------------	-----------

Environmental Specifications

Operating Temperature	-5 °C to +60 °C (+23 °F to +140 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Relative Humidity	Up to 95%, non-condensing
Environmental Space	Indoor Outdoor
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	10
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

