64685043-10 | 6468 5 043-10



LSA-PLUS® Disconnection Module, cat 3, 2/10, PROFIL mounting

Product Classification

Regional AvailabilityAustralia/New ZealandProduct TypeDisconnection module

Product Brand LSA-PLUS®
Product Series LSA-PLUS

General Specifications

ANSI/TIA Category 3

Color White

Mounting PROFIL rods

Pairs, quantity 10

Termination Punchdowns, minimum 200 times

Termination Tool LSA-PLUS Punchdown tool

Termination Type IDC

Electrical Specifications

Contact Resistance, maximum3 mOhmCurrent Rating, maximum2 ADielectric Strength2 kVInsulation Resistance, minimum50 GOhm

Material Specifications

Contact Base Material Brass
Contact Plating Material Silver

Material Type Polybutylene terephthalate (PBT)

COMMSC PE®

64685043-10 | 6468 5 043-10

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Environmental Space Indoor | Outdoor

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 10

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

