

CY9865-000 | MX6-FMCKOLKD1050

OMX Fiber Termination Block with IFC cable, 144 LC/UPC, singlemode, putty white, left, 50 meters, Stub tail at far end

OBSOLETE

This product was discontinued on: December 30, 2018

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch block, with IFC cable
Product Brand	OMX600®
Product Series	OMX

General Specifications

Functionality	Patching
Application	Used in OMX-style frames only
Body Style	Left orientation
Cable Exit Location	Upward
Cable Type	IFC - Stranded
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	Stub tail
Rack Type	OMX
Shelf Movement	Hinged
Total Ports, quantity	144

Dimensions

Height	373.126 mm 14.69 in
Width	203.2 mm 8 in
Depth	283.21 mm 11.15 in
Cable Length	50

CY9865-000 | MX6-FMCKOLKD1050

Material Specifications

Finish Powder coated
Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity 1