FD3-MK072J00M0ME0A



Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000
General Specifications	
Access	Front
Adapters, quantity	72
Cable Type	Pigtails - Stranded
Color	Putty white
Fibers per Feeder Cable, quantity	12
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	72
Splitter Slots, quantity	9
Dimensions	
Height	533.4 mm 21 in
Width	533.4 mm 21 in
Depth	368.3 mm 14.5 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small
Material Specifications	
Finish	Powder coated
Material Type	Steel

IFDH 3000 Indoor Fiber Distribution Hub, 72F, APC

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



FD3-MK072J00M0ME0A

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Environmental Space

Indoor

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

