

FD3-MM216J00V00E0B



IFDH 3000 Indoor Fiber Distribution Hub, 216F, SC/APC, loose tube /stranded pigtails, spliced input, 24F feeder

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Access	Front
Adapters, quantity	216
Cable Type	Pigtails - Stranded
Color	Putty white
Distribution Cables, quantity	3
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	24
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	216
Splitter Slots, quantity	18

Dimensions

Height	368.3 mm 14.5 in
Width	533.4 mm 21 in
Depth	368.3 mm 14.5 in
Enclosure Size	Medium

Material Specifications

Finish	Powder coated
---------------	---------------

FD3-MM216J00V00E0B

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

