FL1-G388NNN2-1000N



FL1000 Fiber Wall Box, 2-door, singlemode LC/UPC, 24-ports, with pigtails and splice tray, 1 cable clamp

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- · Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFI 1000

General Specifications

Application Patching | Splicing

Adapter Packs Included, quantity 2
Adapters, quantity 12
Cable Clamps, quantity 1

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable TypePigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface LC/UPC
Mounting Wall

Splicing Type Heat shrink, mass fusion

Total Fibers, quantity 24

Total Ports, quantity 24

Dimensions

 Height
 433 mm | 17.047 in

 Width
 511 mm | 20.118 in


COMMSC PE°


FL1-G388NNN2-1000N

Depth

156.97 mm | 6.18 in

Outline Drawing





Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

COMMSCOPE®

FL1-G388NNN2-1000N

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

