FL1-G388NNN2-1210N



FL1000 Fiber Wall Box, 2-door, singlemode LC/UPC, 24-ports, with pigtails and splice tray, 1 cable clamp, 2 compression fittings, 1 grounding kit

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFL1000

General Specifications

Application Patching | Splicing

Adapter Packs Included, quantity 2
Adapters, quantity 12
Cable Clamps, quantity 1

Cable Compression Fittings, quantity 2

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable TypePigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface LC/UPC
Mounting Wall

Splicing Type Heat shrink, mass fusion

Total Fibers, quantity 24

Total Ports, quantity 24

Dimensions

COMMSC PE®


FL1-G388NNN2-1210N


 Height
 433 mm | 17.047 in

 Width
 511 mm | 20.118 in

 Depth
 156.97 mm | 6.18 in

Outline Drawing





Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Included One grounding kit

Packaging quantity 1

Packaging Type Bag | Carton

COMMSCOPE®

FL1-G388NNN2-1210N

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

