760087692 | RFE-MOD-024-8W-MPO-LC02-KRD



ReadyPATCH® Singlemode Keyed Module, 24 LC ports, red

• Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®Product TypeFiber module

Product Brand ReadyPATCH® | TeraSPEED®

General Specifications

Functionality Breakout

Adapters, quantity, front 12
Adapters, quantity, rear 2

Color, frontRedColor, rearGray

Interface, front LC/UPC

 Interface Feature, front
 Keyed

 Interface, rear
 MPO

 Interface, rear
 MPO

 Interface Feature, rear
 Male

Polarity Method B

Shuttered Yes

Total Fibers, quantity 24

Total Ports, quantity, front 24

Dimensions

 Height
 27.94 mm | 1.1 in

 Width
 129.54 mm | 5.1 in

 Depth
 127 mm | 5 in

Optical Specifications

Fiber Mode Singlemode

Page 1 of 3

760087692 | RFE-MOD-024-8W-MPO-LC02-KRD

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating0.3 dBInsertion Loss Change, temperature0.3 dBInsertion Loss, maximum1.15 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

460117419 - LazrSPEED® LC Duplex Hybrid Keyed Adapter,

* Footnotes

Insertion Loss Change, matingMaximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



460117419

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Red

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber adapterProduct BrandLazrSPEED®

General Specifications

Body StyleDuplexColorRedInterfaceLC/UPCInterface FeatureKeyedMountingNo flangeShutteredNo

Shuttered No
Total Ports, quantity 2

Transmission Standards TIA/EIA-568-B.3 | TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material Zirconia

Optical Specifications

Fiber Mode Multimode | Singlemode

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

