

760209940 | HD-1U



High Density 1U modular cassette sliding Panel, accepts (4) G2 modules or MPO panels, providing up to 48 duplex LC ports, or up to 32 MPO ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	HD

General Specifications

Application	Accepts four G2 modular cassettes
Color	Black Silver
Intelligence Type	iPatch® ready
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	541.78 mm 21.33 in
Material Thickness	0.9 mm 0.035 in

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Packaging quantity 1
Weight, net 5.625 kg | 12.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

