



OCFPS Fiber Optic Splitter Panel, one 2x32, symmetrical, planar, singlemode, LC/APC, 1U, 19 in, gray

## OBSOLETE

This product was discontinued on: September 18, 2023

### Replaced By:

1RU-SP1232001      1RU panel, 2X32 split ratio, 1 splitter, LC/APC connectors  
1RU SPLTR PNL 2X32 APC/LC

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter patch panel
<b>Product Series</b>	OCFPS

## General Specifications

<b>Device Type</b>	Patch panel
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	2 x 32 splitter
<b>Interface, front</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	43.5 mm   1.713 in
<b>Width</b>	440 mm   17.323 in
<b>Depth</b>	210 mm   8.268 in

## Ordering Tree

OCFPS 1U - X X X X X X

**Shelf Type**

1HU	1 RU High 19" wide
-----	--------------------

**Splitter Grade**

A	FBT type
P	Planar grade P
O	Planar grade O (low loss)

**Number of Splitters**

	Shelf type 1	
	Grade A	Grade P/O
1 x 2	16	-
2 x 2	16	-
1 x 4	-	6
2 x 4	-	6
1 x 8	-	6
2 x 8	-	6
1 x 16	-	2
2 x 16	-	2
1 x 32	-	2
2 x 32	-	1
1 x 64	-	1
2 x 64	-	1

**Connector Type**

S1	SC/UFC
S2	SC/APC 8°
S3	SC/APC 9°
L1	LC/UFC
L2	LC/APC

**Split Ratio**

00	Symmetrical
----	-------------

**Number of Output Ports**

02	... x 2 splitter
04	... x 4 splitter
08	... x 8 splitter
16	... x 16 splitter
32	... x 32 splitter
64	... x 64 splitter

**Number of Input Ports**

1	1 x ...splitter
2	2 x ...splitter

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS

ROHS

UK-ROHS

**Classification**

Below maximum concentration value

Compliant

Compliant

