FL1-G3JJNNN2-1100N



FL1000 Fiber Wall Box, 2-door, singlemode SC/APC, 12-ports, with pigtails and splice tray, 1 cable clamp, 1 compression fitting

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- · Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

 Regional Availability
 North America

 Product Type
 Fiber wall box

 Product Series
 FL1000

General Specifications

Application Patching | Splicing

Adapter Packs Included, quantity 2

Adapters, quantity 12

Cable Clamps, quantity 1

Cable Compression Fittings, quantity 1

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable TypePigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/APC
Mounting Wall

Splicing Type Heat shrink, mass fusion

Total Fibers, quantity 12

Total Ports, quantity 12

Dimensions

Height 433 mm | 17.047 in


Page 1 of 3


FL1-G3JJNNN2-1100N

Width 511 mm | 20.118 in

Depth 156.97 mm | 6.18 in

Outline Drawing





Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications



FL1-G3JJNNN2-1100N

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

