FL1-J3888882-4002N



FL1000 Fiber Wall Box, 2-door, singlemode LC/UPC, 96-ports, with pigtails and splice tray, 4 cable clamps, 2 strength member tie-offs

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- · Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFL1000

General Specifications

Application Patching | Splicing

Adapter Packs Included, quantity 8

Adapters, quantity 48

Cable Clamps, quantity 4

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Wall

Cable TypePigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface LC/UPC

Splicing Type Heat shrink, mass fusion

Total Fibers, quantity 96

Total Ports, quantity 96

Dimensions

Mounting

 Height
 708 mm | 27.874 in

 Width
 669 mm | 26.339 in


Page 1 of 3



FL1-J3888882-4002N

Depth 235.97 mm | 9.29 in

Outline Drawing



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Included Two tie-off adapters

Packaging quantity

Packaging Type Bag | Carton



FL1-J3888882-4002N

Regulatory Compliance/Certifications

Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

