RCP-C3KAPUK03100



RapidFiber® Termination Panel, 144-Position 3RU, singlemode, LC/UPC to 24-fiber and LC cabled module, 31 m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

General Specifications

Functionality Patching

Body Style Symmetrical

Cable Exit Location Rear, left side

 Cable Stub Type
 Indoor, microcable

Color Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontLC/UPCInterface, rearLC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 3

Shelf MovementSlidingTotal Fibers, quantity144Total Ports, quantity72

Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

Height 133.35 mm | 5.25 in

COMMSCOPE®


RCP-C3KAPUK03100

 Width
 482.6 mm | 19 in

 Depth
 381 mm | 15 in

Cable Length 31 m | 101.706 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

COMMSCOPE®

RCP-C3KAPUK03100

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+55 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +131 $^{\circ}\text{F}$)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

