

# 760206565 | 360DMis-24LCA-SM



G2 LL Singlemode MPO 12 distribution module, 24 LC APC to 2x12f MPO's pinned, internal shutters

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	InstaPATCH® 360
Product Series	G2

## General Specifications

Functionality	Breakout
Color, front	Green
Color, rear	Gray
Interface, front	LC/APC
Interface, rear	MPO
Interface Feature, rear	Key up/up   Pinned
Polarity	Method B
Shuttered	Yes
Total Fibers, quantity	24

## Dimensions

Height	25.51 mm   1.004 in
Width	95.91 mm   3.776 in
Depth	119.69 mm   4.712 in

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	1.05 dB

Environmental Specifications

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	CE   CSA   UL

Packaging and Weights

Packaging quantity	1
Weight, net	0.109 kg   0.24 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

