FD3-AC144J00GBBP2



FDH 3000 Fiber Distribution Extra Small Cabinet, 144F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F

Alternative products available:

FD3-AC144J00GBBP2-US FDH 3000 Fiber Distribution Extra Small Cabinet, 144F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F, Build America Buy America (BABA)

Product Classification

Regional Availability North America

Fiber distribution hub **Product Type**

Product Series FDH 3000

General Specifications

Access Front

Cable Type Armored - Single Loose Tube

Color Putty white

Distribution Cables, quantity 1

Distribution Ports, quantity 144

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity

Dimensions

Height 914 mm | 35.984 in Width 533 mm | 20.984 in **Depth** 356 mm | 14.016 in **Cable Length** 30.48 m | 100 ft

COMMSCOPE®

FD3-AC144J00GBBP2

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

