FD3-AC144J00JABP2



FDH 3000 Fiber Distribution Extra Small Cabinet, 144F, SC/APC, no splitters, die. loose tube, 100 ft, 24F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 144

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 9

Dimensions

 Height
 914 mm | 35.984 in

 Width
 533 mm | 20.984 in

Depth 356 mm | 14.016 in

Cable Length 30.48 m | 100 ft

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Steel

COMMSCOPE®

FD3-AC144J00JABP2

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

