## FD3-AJ576J00JABP7



FDH 3000 Fiber Distribution Large Cabinet, 576F, SC/APC, no splitters, dielectric loose tube, 100 ft, 72F

## Product Classification

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	FDH 3000	
General Specifications		
Access	Front and rear door	
Cable Type	Dry Dielectric - Loose Tube	
Color	Putty white	
Distribution Cables, quantity	8	
Distribution Ports, quantity	576	
Fibers per Distribution Cable, quantity	72	
Fibers per Feeder Cable, quantity	72	
Interface, Input	SC	
Interface Feature, Input	APC	
Mounting	Pad	
Dimensions		
Height	1,238.25 mm   48.75 in	
Width	1,220.47 mm   48.05 in	
Depth	497.33 mm   19.58 in	
Cable Length	30.48 m   100 ft	
Enclosure Size	Large	
Material Specifications		
Finish	Powder coated	
Material Type	Aluminum	

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024



## FD3-AJ576J00JABP7

## **Environmental Specifications**

JU

Environmental Space		Above ground	
Packaging and Weights			
Packaging quantity		1	
Packaging Type		Pallet	
Regulatory Compliance/Certifications			
Agency	Classification		
CHINA-ROHS	Above maximum concentration value		
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance		
ROHS	Compliant/Exempted		
UK-ROHS	Compliant/Exempted		

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024

