

# TPNP-24APC10-UN

---



RJ45 Patch Panel, category 6A, 24-port, 1 RU, unloaded

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	RJ45 patch panel

## General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Color</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	RJ45 jack
<b>Panel Mounting</b>	Flush
<b>Panel Style</b>	Angled
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Termination Type</b>	IDC
<b>Total Ports, quantity</b>	24
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   ISO/IEC 11801 Class EA

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Steel
----------------------	---

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

# TPNP-24APC10-UN

---

**Packaging Type**

Bag | Box