760235611 | OCM6-SP11ZS2-30DB1



OCM6 Fiber Optic Splitter Module, Planar, one 1x64 Splitter, singlemode, SC/APC, symmetrical split ratio, butt style, 3 m pigtails

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM	
Functionality	Splitting	
Technology Type	Planar lightwave circuit (PLC)	
Application	For use with BUDI wall boxes	
Circuits, quantity	1	
Distribution Type	1 x 64 splitter	
Interface, Input	SC	
Interface Feature, Input	APC	
Interface, Output	SC	
Interface Feature, Output	APC	
Split Ratio	Symmetrical	
Splitter, quantity	1	
.		

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	3 m 9.843 ft

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 19, 2022



760235611 | OCM6-SP11ZS2-30DB1

Pigtail Length, Output Pigtail Diameter 3 m | 9.843 ft 1.8 mm | 0.071 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency

Classification

1

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 19, 2022

