760238084 | DM08iP-24LC-SM-ULL





Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber module

Product Brand SYSTIMAX ULL | TeraSPEED®

General Specifications

Functionality Breakout

Adapters, quantity, front 24
Adapters, quantity, rear 3
Color, front Blue

Color, rear Blue

Data Module Type Standard

Intelligence Type iPatch® ready

Interface, frontLC/UPCInterface, rearMPO

Interface Feature, rear Key up | MPO Non-Pinned

Polarity Method B Enhanced (ULL)

Shuttered Yes
Total Fibers, quantity 24
Total Ports, quantity, front 24

Dimensions

 Height
 24.64 mm | 0.97 in

 Width
 94 mm | 3.701 in



760238084 | DM08iP-24LC-SM-ULL

Depth 113.28 mm | 4.46 in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2Insertion Loss, maximum0.6 dB

Environmental Specifications

Qualification StandardsTIA/EIA-568-C.3Safety StandardcUL US 1863

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

