

760242266 | FD-8-1U-B-LS



1RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 10 MPO-8 and 40 duplex LC ports, OM4, Enhanced Method B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Color	Black
Interface, front	LC/UPC MPO
Interface Feature, front	Pinned
Rack Units	1
Total Ports, quantity	40

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	292.1 mm 11.5 in

Optical Specifications

Insertion Loss, maximum	0.35 dB
--------------------------------	---------

Environmental Specifications

Safety Standard	UL 60950
------------------------	----------

Packaging and Weights

Packaging quantity	1
Weight, net	2.087 kg 4.6 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Above maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant/Exempted
Compliant/Exempted

