## CW8580-001 | IFDB-SPLT-1\*4-S2

#### IFDB Optical Splitter Module, plug & play, SC/APC ports, 1 x 4 splitter

#### **Product Classification**

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series IFDB

#### General Specifications

**Device Type** Plug-and-play module

**Functionality** Splitting

Circuits, quantity 1

Distribution Type1 x 4 splitterInterface, frontSC/APCInterface, InputSC/APCInterface, OutputSC/APC

**Split Ratio** Symmetrical

Splitter, quantity 1

#### Optical Specifications

Wavelength Range 1260–1635 nm

#### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





# CW8580-001 | IFDB-SPLT-1\*4-S2

