

# CY4075-000 | OCM6-SP11WSL2-61CI1

---

OCM6 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, LC/APC, symmetrical split ratio, in-line style, 61 cm pigtails



## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM6

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use with BUDI wall boxes
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 32 splitter
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	130 mm   5.118 in
<b>Width</b>	49.8 mm   1.961 in
<b>Depth</b>	16.5 mm   0.65 in
<b>Pigtail Length, Output</b>	0.61 m   2.001 ft
<b>Pigtail Diameter</b>	1.8 mm   0.071 in

Packaging and Weights

**Packaging quantity** 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

