

# 760092007 | RK3-45AM



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) M6 Tapped Rails, Black

## OBSOLETE

This product was discontinued on: November 30, 2018

### Replaced By:

760090118  
RK3-45S

Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	45
<b>Rail Mounting Hole</b>	M6

## Dimensions

<b>Height</b>	2,133.6 mm   84 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	518.16 mm   20.4 in
<b>Depth</b>	381 mm   15 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

# 760092007 | RK3-45AM

---

## Mechanical Specifications

**Load Rating** 453.592 kg | 1000 lb

## Packaging and Weights

**Included** Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

**Packaging quantity** 1

**Packaging Type** Flat packed

**Weight, net** 12.7 kg | 27.999 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system