



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 3 ft ( mm) H - 19 in (482.6 mm) Alu (17U) 12-24 Tapped Rails, Black

## OBSOLETE

This product was discontinued on: November 30, 2018

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	17
<b>Rail Mounting Hole</b>	#12-24

## Dimensions

<b>Height</b>	914.4 mm   36 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	518.16 mm   20.4 in
<b>Depth</b>	381 mm   15 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

## Mechanical Specifications

<b>Load Rating</b>	453.592 kg   1000 lb
--------------------	----------------------

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Forty #12-24 x 1/2 in mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

**Packaging quantity** 1

**Packaging Type** Flat packed

**Weight, net** 15.88 kg | 35.009 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

