760109496 | 360G2 Cartridge 12-LC-SM-BL-PIGTAILS



360G2 Singlemode Fiber Cassette 12 LC, with pigtails, iPatch Ready

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Portfolio	CommScope®	
Product Type	Fiber cassette with pigtails	
Product Series	G2	
General Specifications		
Color, front	Blue	
Intelligence Type	iPatch® ready	
Interface, front	LC/UPC	
Interface, rear	Stranded pigtail	
Shuttered	No	
Total Ports, quantity, front	12	
Dimensions		
Height	25.908 mm 1.02 in	
Width	94.996 mm 3.74 in	
Depth	123.012 mm 4.843 in	
Optical Specifications		
Fiber Mode	Singlemode	
Fiber Type	G.657.A1	
Insertion Loss, maximum	0.34 dB	
Environmental Specifications		

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025



760109496 | 360G2 Cartridge 12-LC-SM-BL-PIGTAILS

Packaging and Weights

Packaging quantity	1
Weight, net	0.098 kg 0.215 lb
Regulatory Compliance/Certifications	

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

