

CB0056-000 | FOMS-FPS-O-SKL1-24

FOMS-FPS Fiber Termination/Splice Panel, 24 LC/UPC, singlemode, 1RU, 19 in, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FOMS-FPS

General Specifications

Functionality	Patching Splicing
Color	Gray
Color, front	Gray
Interface, front	LC/UPC
Rack Type	EIA 19 in EIA 23 in ETSI 600 mm
Rack Units	1
Shelf Movement	Hinged
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Ordering Tree

FOMS-FPS - X - X X XX - XX

Chassis type				Number of pigtails and/or connector ports							
○ 19" - 44 mm high				48 (for LC and MU only)							
				24							
Shelf type				16 (not for LC and MU)							
P Patching only (jumpers, break-out cable)				12 (not for LC and MU)							
S Splicing and patching (loose tube cable, ribbon, IFC)				0							
Tray type/pigtails											
Secondary coated pigtails included	Splice protector	Jumpers leave shelf									
		Right front	Left front								
Not applicable (patching only)		N	M								
No	SMOUV*	E	G								
No	ANT*	F	H								
Yes	SMOUV*	I	K								
Yes	ANT*	J	L								
Connector adapter with retainer											
NN No connectors/pigtails											
Min.return loss	SC	FC	E2000	LC	DIN	ST	MU				
Single Mode Standard											
45 dB (PC)					DO	TO					
50 dB (UPC)	S1	F1		L1				U1			
60 dB (APC 8°)	S2	F2	E9	L2							
60 dB (APC 9°)	S3										
Single Mode Low Loss											
50 dB (UPC)	S6										
60 dB (APC 8°)	S7		E8								
60 dB (APC 9°)	S8										
Single Mode Consumer Grade											
50 dB (UPC)	SC	FC		LC							
60 dB (APC 8°)	SD	FD		LD							
Multi Mode											
50/900 μ	S5D	F5D	E5D	L5D		T5D					
62.5/900 μ**	S5E	F5E	E5E	L5E		T5E					

* Splice protectors not included in the kit
 ** In case of adapters only (no pigtails included) use S5D, F5D, E5D, L5D and T5D.

Material Specifications

Material Type Ethylene-propylene (EP) | Polyethylene terephthalate (PET)

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

