

FIST-GPS2 Fiber Termination/Splice Panel, LC/UPC, singlemode, 3RU, with 6 trays, 19 in, gray

## Product Classification

|                              |                          |
|------------------------------|--------------------------|
| <b>Regional Availability</b> | EMEA                     |
| <b>Portfolio</b>             | CommScope®               |
| <b>Product Type</b>          | Fiber patch/splice panel |
| <b>Product Brand</b>         | FIST®                    |
| <b>Product Series</b>        | FIST-GPS2                |

## General Specifications

|                         |                                    |
|-------------------------|------------------------------------|
| <b>Functionality</b>    | Patching   Splicing                |
| <b>Application</b>      | Used in FIST-GR3-style frames only |
| <b>Color</b>            | Gray                               |
| <b>Color, front</b>     | Gray                               |
| <b>Interface, front</b> | LC/UPC                             |
| <b>Rack Type</b>        | EIA 19 in   ETSI 600 mm            |
| <b>Rack Units</b>       | 3                                  |
| <b>Shelf Movement</b>   | Sliding                            |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 133.35 mm   5.25 in |
| <b>Width</b>  | 482.6 mm   19 in    |

## Material Specifications

|                      |                  |
|----------------------|------------------|
| <b>Finish</b>        | Powder coated    |
| <b>Material Type</b> | Galvanized steel |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -5 °C to +45 °C (+23 °F to +113 °F)  |
| <b>Storage Temperature</b>   | -30 °C to +60 °C (-22 °F to +140 °F) |

# CC1513-000 | FIST-GPS2-I-AML1-6

---

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

