

CU7578-000 | FOMS-FPS-0-SIL1-24

FOMS-FPS Fiber Termination/Splice Panel, 24 LC/UPC, singlemode, 1RU, 19 in, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FOMS-FPS

General Specifications

Functionality	Patching Splicing
Color	Gray
Color, front	Gray
Interface, front	LC/UPC
Rack Type	EIA 19 in EIA 23 in ETSI 600 mm
Rack Units	1
Shelf Movement	Hinged
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Ordering Tree

CU7578-000 | FOMS-FPS-0-SIL1-24

FOMS-FPS - X - X X XX - XX

Chassis type				Number of pigtails and/or connector ports							
<input type="radio"/>	19" - 44 mm high			48	(for LC and MU only)						
Shelf type				24							
<input type="radio"/>	Patching only (jumpers, break-out cable)			16	(not for LC and MU)						
<input type="radio"/>	Splicing and patching (loose tube cable, ribbon, IFC)			12	(not for LC and MU)						
				0							
Tray type/pigtails				Connector adapter with retainer							
Secondary coated pigtails included		Splice protector		NN No connectors/pigtails							
				Min.return loss							
				SC	FC	E2000	LC	DIN	ST	MU	
Not applicable (patching only)				Single Mode Standard							
				45 dB (PC)							
				50 dB (UPC)							
				S1	F1		L1		DO	TO	
				60 dB (APC 8°)							
				S2	F2	E9	L2				
				60 dB (APC 9°)							
				S3							
				Single Mode Low Loss							
				50 dB (UPC)							
				S6							
				60 dB (APC 8°)							
				S7		E8					
				60 dB (APC 9°)							
				S8							
				Single Mode Consumer Grade							
				50 dB (UPC)							
				SC	FC		LC				
				60 dB (APC 8°)							
				SD	FD		LD				
				Multi Mode							
				50/900 μ							
				S5D	F5D	E5D	L5D		T5D		
				62.5/900 μ**							
				S5E	F5E	E5E	L5E		T5E		

* Splice protectors not included in the kit
 ** In case of adapters only (no pigtails included) use S5D, F5D, E5D, L5D and T5D.

Material Specifications

Material Type Ethylene-propylene (EP) | Polyethylene terephthalate (PET)

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

