

EF3999-000 | FIST-GPS3-Q-AML1-6

FIST-GPS3 Fiber Panel, loaded with 6 GPST Patch/Splice Trays, singlemode LC/UPC, 3RU, gray

Product Classification

| | |
|------------------------------|--------------------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Brand | FIST® |
| Product Series | FIST-GPS3 |

General Specifications

| | |
|-------------------------|-------------------------------------|
| Functionality | Patching Splicing |
| Application | Used in FIST-GR3F-style frames only |
| Color | Gray |
| Color, front | Gray |
| Interface, front | LC/UPC |
| Rack Type | EIA 15 in |
| Rack Units | 3 |
| Shelf Movement | Sliding |

Dimensions

| | |
|---------------|--------------------|
| Height | 125 mm 4.921 in |
| Width | 381 mm 15 in |
| Depth | 280 mm 11.024 in |

Material Specifications

| | |
|----------------------|------------------|
| Finish | Powder coated |
| Material Type | Galvanized steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Environmental Specifications

| | |
|------------------------------|-------------------------------------|
| Operating Temperature | -5 °C to +45 °C (+23 °F to +113 °F) |
|------------------------------|-------------------------------------|

EF3999-000 | FIST-GPS3-Q-AML1-6

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

