468349-000 | XAGA1000-E4-KIT-M478



XAGA® 1000 Copper Closure, pressurized, heat shrink, 37 inch sheath opening, 7.8 inch splice bundle diameter

- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional AvailabilityLatin America | North AmericaProduct TypePressurized heat shrink closure

Product Brand XAGA®

Product Series XAGA 1000

General Specifications

Application For use with Polyethylene and metal jacketed cables

Branch-off ClipTo be ordered seperately

Cable Capacity, maximum 4

Cable Sealing TypeHotmelt adhesive

Color In-line Black

Mounting Duct | Manhole

Splice Protection TypeMetal canister with valve


Dimensions

Single Cable Diameter, minimum66.04 mm | 2.6 inSplice Bundle Diameter, maximum198.12 mm | 7.8 inSheath Opening, nominal939.8 mm | 37 in

Dimension Drawing

Page 1 of 2





Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible

stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity

wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

