


760236503 | PNL-CS-24LCX



LazrSPEED® Splicing cassette, 24LC , No Pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette

General Specifications

Adapter Color	Aqua
Interface, front	LC/UPC
Interface, rear	No pigtail
Total Fibers, quantity	0
Total Ports, quantity, front	12

Dimensions

Height	28.956 mm 1.14 in
Width	104.648 mm 4.12 in
Depth	165.354 mm 6.51 in

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

760236503 | PNL-CS-24LCX

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant

UK-ROHS

Compliant

