# 760239339 | SCIL-B-24-1-S4-GV



SCIL-B Fiber splice closure, in-line, with 4 gel cable sealing kits, 1 pre-installed 24-splice tray and SMOUV protectors, 2 ground feedtrough lug, air valve

- Leverages proven FOSC™ fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Product Type In-line, rectangular fiber closure

Product Brand SCIL™
Product Series SCIL-B

General Specifications

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Round

**Cable Ports Quantity, total** 4 multi-out ports (24 cables)

Cable Sealing Type Compressed gel

Closure Sealing Type Side latch

Color In-line Black

Ground Feed-through Lugs, quantity 2

Mounting Pole | Strand | Wall

Network Area Type Drop

Splice Tray Included, quantity

**Splice Tray Type Included** 24-way, heat shrink

Splicing Capacity, Single Fusion, maximum 96
Splicing Capacity, Single Splice, 12 fibers, maximum 96

**Splicing Type, Supported** Single fusion



# 760239339 | SCIL-B-24-1-S4-GV

#### **Dimensions**


 Height
 106 mm | 4.173 in


 Width
 182 mm | 7.165 in

 Length
 369 mm | 14.528 in

 Main Cable Diameter, maximum
 22 mm | 0.866 in

#### Ordering Tree





#### Material Specifications

Material Type Rugged polymer

## **Environmental Specifications**

Environmental SpaceAbove ground| Below groundQualification StandardsIEC 60529, IP68 + 2 m waterheadWater ResistanceFlash test valve at 5 psi (40 kPa)

Packaging and Weights

Included SMOUV splice protectors (24)

COMMSCOPE®

# 760239339 | SCIL-B-24-1-S4-GV

Packaging quantity

Packaging Type Box | Carton

**Weight, net** 1 kg | 2.205 lb

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

1

