

XAGA® 550 Copper Closure, unpressurized, heat shrink, 450 mm sheath opening, 150 mm splice bundle diameter



OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America
Product Type	Unpressurized heat shrink closure
Product Brand	XAGA®
Product Series	XAGA 550


General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	3
Cable Sealing Type	Hotmelt adhesive
Closure Style	In-line
Color	Black
Mounting	Duct Manhole
Splice Protection Type	Metal canister

Dimensions

Single Cable Diameter, minimum	42 mm 1.654 in
Splice Bundle Diameter, maximum	150 mm 5.906 in
Sheath Opening, nominal	450 mm 17.717 in

Dimension Drawing



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips

Packaging quantity 1

Packaging Type Bag | Carton