



G2 Splice Cassette, 24LC/UPC with internal shutters, OS2, with pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Series</b>	G2

## General Specifications

<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Pairs, straight
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	26.416 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in
<b>Depth</b>	165.354 mm   6.51 in

## Material Specifications

<b>Alignment Sleeve Material</b>	Zirconia
----------------------------------	----------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB

**Return Loss, minimum** 50 dB

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** SMOUV holder | SMOUV splice protection

**Packaging quantity** 1

**Weight, net** 0.147 kg | 0.324 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

