

# 760245736 | CHD-SP-12LA-SM-AS-LL



CHD Singlemode Splice Cassette, 12LC/APC, with dust plugs and pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Series</b>	CHD

## General Specifications

<b>Adapter Color</b>	Green
<b>Color, front</b>	Green
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Method A   Pairs, straight
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Height</b>	12.446 mm   0.49 in
<b>Width</b>	83.82 mm   3.3 in
<b>Depth</b>	184.658 mm   7.27 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.4 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
--------------------------------	---------------------------

# 760245736 | CHD-SP-12LA-SM-AS-LL

---

**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Included** Single Fusion Splice Protection Sleeves

**Packaging quantity** 1

**Weight, net** 0.095 kg | 0.21 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

FST-ACC005 – Fiber Optic Protective Splice Sleeve, 1 package

# FST-ACC005

---



Fiber Optic Protective Splice Sleeve, 1 package

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber protection sleeve

## General Specifications

<b>Splicing Type</b>	Heat shrink, single fiber fusion
----------------------	----------------------------------

## Environmental Specifications

<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
----------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

