

# 7712946-00

---

Rack 19" 47 HU 800x800 perforated

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

**Product Type** Network cabinet, with perforated doors

## General Specifications

**Color** Gray

**Mounting** M6 Cage nut rail mounting

**Note** Static load rating is 1000 kg

**Rack Type** EIA 19 in

## Dimensions

**Height** 2200 mm | 86.614 in

**Height, guide rails** 2,089.15 mm | 82.25 in

**Width** 800 mm | 31.496 in

**Depth** 800 mm | 31.496 in

## Electrical Specifications

**Electrical Safety Standard** UL | cUL

**Voltage Range** On-site configuration dependant

## Material Specifications

**Material Type** Galvanized sheet metal | Powder-coated, textured

## Packaging and Weights

**Height, packed** 2380 mm | 93.701 in

**Width, packed** 960 mm | 37.795 in

**Depth, packed** 1222 mm | 48.11 in

**Included** Cables ducts (2) | Cage nuts M6 (92) | Grounding cables (10) | Grounding rail (1) | Guide rails (20) | Raised head screws M6 (92)

# 7712946-00

---

<b>Packaging quantity</b>	1
<b>Weight, gross</b>	275 kg   606.27 lb
<b>Weight, net</b>	160 kg   352.739 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

