

# 7712980-00

---



Rack, 4-Post, 19" 47 HU 600x600 open frame

**OBSOLETE**

This product was discontinued on: June 30, 2022

## Product Classification

**Product Type** 4 post rack

## General Specifications

**Color** Gray  
**Mounting** M6 Cage nut rail mounting  
**Note** Static load rating is 1000 kg  
**Rack Type** EIA 19 in

## Dimensions

**Height** 2200 mm | 86.614 in  
**Height, guide rails** 2,089.15 mm | 82.25 in  
**Width** 600 mm | 23.622 in  
**Depth** 600 mm | 23.622 in

## Electrical Specifications

**Electrical Safety Standard** UL | cUL  
**Voltage Range** On-site configuration dependant

## Material Specifications

**Material Type** Galvanized sheet metal | Powder-coated, textured

## Packaging and Weights

**Height, packed** 2380 mm | 93.701 in

# 7712980-00

---

<b>Width, packed</b>	760 mm   29.921 in
<b>Depth, packed</b>	1222 mm   48.11 in
<b>Included</b>	Cables ducts (2)   Cage nuts M6 (92)   Grounding cables (10)   Grounding rail (1)   Guide rails (20)   Raised head screws M6 (92)
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	165 kg   363.762 lb
<b>Weight, net</b>	60 kg   132.277 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system